



GreenVision All-in-one Solar Street Light

BRP715 LED70 CW Solar 5

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and MPPT charge controller built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting. Adjustable LED module for better distribution of light when required.

Product data

General Information	
Driver included	Yes
Light Technical	
Luminous Flux	7,200 lm
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	>70
Operating and Electrical	
Battery type	LiFePO4
Battery ampere hour	18 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	18 V
Panel peak wattage	40 W
Charge controller type	MPPT
Cable	-
Grid connection type	Off grid

Controls and Dimming	
Dimmable	Yes
Configurability	Configurable
Solar dimming profile	Dimming along with microwave motion sensor
Mechanical and Housing	
Housing Color	Black
Overall length	750 mm
Overall width	366 mm
Overall height	133 mm
Dimensions (Height x Width x Depth)	133 x 366 x 750 mm
Material	Aluminum
Battery location	Inbuilt
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	10.190 kg
Approval and Application	
CE mark	Yes

GreenVision All-in-one Solar Street Light

Ambient temperature range	-10 °C to 55 °C
Product Data	
Order product name	BRP715 LED70 CW Solar 5
Full product name	BRP715 LED70 CW Solar 5
Full product code	871951495422900
Order code	911401626608

Material Nr. (12NC)	911401626608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514954229
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514954229

Dimensional drawing

