



SmartBright Highbay

BY239P LED195/NW PSU GM G2

SmartBright Highbay, 150 W, 19500 lm, 4000 K

SmartBright Highbay is a high efficient and reliable LED luminaire. Designed as the point to point replacement for HPI 250W/400W luminaires, it offers customers all the benefits of LED lighting – reduced energy consumption, longer service time and less maintenance. In addition, with using high quality of the optical cover, it provides an excellent quality of light, which effectively improves the comfort of your environment.

Product data

General Information	
Light source engine type	LED
Value ladder	Value

Light Technical	
Luminous Flux	19,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Effective projected area	0.06 m ²

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	42 A
Power Consumption	150 W
Power Factor (Fraction)	0.95
Number of products on MCB of 16 A type B	6

Protection class IEC	Safety class I
----------------------	----------------

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Dark gray
Optical cover finish	Clear
Overall height	93 mm
Overall diameter	319 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Lens
Net Weight (Piece)	1.890 kg

SmartBright Highbay

Approval and Application

Insulation Coverage Rating	Partial coverage acc. to IEC 60598-1 8.1
Flammability mark	-
CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.385, 0.380) SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BY239P LED195/NW PSU GM G2
--------------------	----------------------------

Full product name	BY239P LED195/NW PSU GM G2
Full product code	871951454105400
Order code	54105400
Material Nr. (12NC)	911401640407
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514541054
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514541054

Dimensional drawing

