



# Ledinaire High-bay

## BY020Z G2 ALU

Ledinaire High-bay, Accessory, Aluminum

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables, simple and flexible installation, either on a hook, or optional bracket. Products can be installed with optional reflectors for lower glare.

### Product data

General Information	
Service tag	No
Value ladder	Value
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Overall length	382 mm
Overall width	382 mm
Overall height	156 mm
Overall diameter	382 mm
Dimensions (Height x Width x Depth)	156 x 382 x 382 mm
Material	Aluminum
Ingress protection code	-
Mech. impact protection code	-
Accessory color	Aluminum

Net Weight (Piece)	0.500 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic
Product Data	
Order product name	BY020Z G2 ALU
Full product name	BY020Z G2 ALU
Full product code	871951453017199
Order code	911401657907
Material Nr. (12NC)	911401657907
Numerator - Quantity Per Pack	1

## Ledinaire High-bay

EAN/UPC - Product/Case	8719514530171
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514939424

### Dimensional drawing

