

BY020Z G2 ALU

911401657907



Ledinaire High-bay, Accessory, Aluminum

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables, simple and flexible installation, either on a hook, or optional bracket. Products can be installed with optional reflectors for lower glare.

General Information

Service tag	No
Value ladder	Value

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall length	382 mm
Overall width	382 mm

Overall height	156 mm
Overall diameter	382 mm
Dimensions (Height x Width x Depth)	156 x 382 x 382 mm
Material	Aluminum
Ingress protection code	-
Mech. impact protection code	-
Accessory color	Aluminum
Net Weight (Piece)	0.500 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	BY020Z G2 ALU
Full product name	BY020Z G2 ALU
Full product code	871951453017199
Order code	53017199
Material Nr. (12NC)	911401657907
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514530171
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514939424

Dimensional drawing

