



# Ledinaire High-bay

## BY020Z G2 ALU

Ledinaire High-bay, Accessory, Aluminum

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables, simple and flexible installation, either on a hook, or optional bracket. Products can be installed with optional reflectors for lower glare.

### Product data

<b>General Information</b>		<b>Net Weight (Piece)</b>		0.500 kg
Service tag	No	<b>Approval and Application</b>		
Value ladder	Value	CE mark	Yes	
<b>Operating and Electrical</b>		EU RoHS compliant	Yes	
Input Voltage	- V	<b>Sustainability Data</b>		
Line Frequency	- Hz	<b>Non-virgin material ratio of the packaging</b>	Cardboard > 80% recycled Plastic >35% recycled	
Protection class IEC	-	<b>Packaging Recyclable content ratio</b>	Cardboard recycling rate > 80% Plastic recycling rate > 40%	
<b>Mechanical and Housing</b>		<b>Packaging Material</b>	Cardboard Plastic	
Overall length	382 mm	<b>Product Data</b>		
Overall width	382 mm	<b>Order product name</b>	BY020Z G2 ALU	
Overall height	156 mm	<b>Full product name</b>	BY020Z G2 ALU	
Overall diameter	382 mm	<b>Full product code</b>	871951453017199	
Dimensions (Height x Width x Depth)	156 x 382 x 382 mm	<b>Order code</b>	53017199	
Material	Aluminum	<b>Material Nr. (12NC)</b>	911401657907	
Ingress protection code	-	<b>Numerator - Quantity Per Pack</b>	1	
Mech. impact protection code	-			
Accessory color	Aluminum			

## Ledinaire High-bay

EAN/UPC - Product/Case	8719514530171
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514939424

### Dimensional drawing

