



Ledinaire High-bay

BY021Z G2 BY022Z G3 ALU

Ledinaire High-bay, Accessory, Aluminum

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables, simple and flexible installation, either on a hook, or optional bracket. Products can be installed with optional reflectors for lower glare.

Product data

General Information	
Service tag	No
Value ladder	Value
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Overall length	480 mm
Overall width	480 mm
Overall height	194 mm
Overall diameter	480 mm
Dimensions (Height x Width x Depth)	194 x 480 x 480 mm
Material	Aluminum
Ingress protection code	-
Mech. impact protection code	-
Accessory color	Aluminum

Net Weight (Piece)	0.800 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic
Product Data	
Order product name	BY021Z G2 BY022Z G3 ALU
Full product name	BY021Z G2 BY022Z G3 ALU
Full product code	871951453016499
Order code	53016499
Material Nr. (12NC)	911401658007
Numerator - Quantity Per Pack	1

Ledinaire High-bay

EAN/UPC - Product/Case	8719514530164
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514939431

Dimensional drawing

