



SmartBright Solar All-in-one Streetlight

BRP010 LED150/757 Solar AIO

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and controller built into the luminaire. Independently tilt-able LED source and pole mounting bracket allows light beam to focus on road, and solar panel towards the sun. Microwave based motion sensor for optimizing battery autonomy.

Warnings and Safety

- The product must be installed in a sunny place that is not shaded by trees, buildings, wall, etc. so that the solar panel can receive the maximum sunlight for charging the battery inside the luminaire.

Product data

General Information		Charge controller type	
Driver included	Yes	Charge controller wattage	MPPT
Warranty period	3 years	Cable	90 W
Light Technical		Grid connection type	-
Luminous Flux	15,000 lm	Control interface	Off grid
Correlated Color Temperature (Nom)	5700 K	Controls and Dimming	
Color rendering index (CRI)	70	Dimmable	Preset Dimming
Operating and Electrical		Configurability	Factory Configurable
Line Frequency	- Hz	Solar dimming profile	-
Battery type	LiFePO4	1. Dusk to 2hours: 100% on motion, 20% with no motion. 2. Next 3hours: 50% on motion, 10% when no motion. 3. Next 7hours: 30% on motion, 10% when no motion.	
Battery ampere hour	30 Ah	Mechanical and Housing	
Battery voltage	25.6 V	Housing Color	Grey
Panel type	Mono crystalline	Overall length	1,367 mm
Panel voltage	36 V		
Panel peak wattage	125 W		

SmartBright Solar All-in-one Streetlight

Overall width	482 mm
Overall height	235 mm
Dimensions (Height x Width x Depth)	235 x 482 x 1367 mm
Material	Metal
Battery location	inbuilt
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Polycarbonate
Net Weight (Piece)	24.490 kg

Approval and Application

EU RoHS compliant	Yes
Ambient temperature range	-10 to +50 °C

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	BRP010 LED150/757 Solar AIO
Full product name	BRP010 LED150/757 Solar AIO
Full product code	872110330885600
Order code	911401659309
Material Nr. (12NC)	911401659309
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103308856
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103308856

Dimensional drawing

