



# RoadFlair Pro

## BRP594 LED389/NW 240W DM PSRD PE GM

RoadFlair Pro, 38900 lm, 240 W, 740 neutral white, depends on driver (1-10V, DALI...), Safety class I

Municipalities value energy saving more than ever, as energy price hikes put increasing pressure on the budgets. Street lighting consumes substantial energy, so large-scale upgrades to energy-efficient LED streetlights are fundamental to cities' cost-saving efforts. RoadFlair Pro has been upgraded to minimize costs while maximizing efficacy, safety, and functionality. And the best part - RoadFlair Pro offers a streamlined design, so it maintains an attractive aesthetic on city streets. These streetlights not only look good, they also offer excellent performance. Future-proof technology combines with high efficacy ( 160 lm/W and 200 lm/W), innovative design, and smart connectivity in a light that makes your street look brighter and better

### Product data

General Information		Line Frequency	
Driver included	Yes		50 or 60 Hz
Value ladder	Specification	Power Consumption	240 W
		Power Factor (Fraction)	0.95
		Connection	Connection unit 5-pole
		Cable	-
		Protection class IEC	Safety class I
Light Technical		Controls and Dimming	
Luminous Flux	38,900 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K	Control interface	depends on driver (1-10V, DALI...)
Luminous Efficacy (rated) (Nom)	160 lm/W		
Color rendering index (CRI)	>70	Mechanical and Housing	
Light source color	740 neutral white	Housing Material	Aluminum die cast
Operating and Electrical			
Input Voltage	220-240 V		

## RoadFlair Pro

Optical cover material	Polycarbonate
Housing Color	Gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Clear dome
Net Weight (Piece)	4.730 kg

### Approval and Application

CE mark	Yes
Ambient temperature range	-40 °C to 50 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
-------------------------	-------

Power consumption tolerance	+/-10%
-----------------------------	--------

### Product Data

Order product name	BRP594 LED389/NW 240W DM PSRD PE GM
Full product name	BRP594 LED389/NW 240W DM PSRD PE GM
Order code	911401672409
Material Nr. (12NC)	911401672409
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

