



Tango G4 LED Flood

BVP431 LED92/CW 220~240V 70W SWB GC

Tango G4 LED Flood, 9200 lm, 70 W, 757 cool white, Safety class I

Philips Tango G4 LED flood lighting is the 4th generation of the Tango LED family. A new range lighting that delivers higher efficacy and has an optimized windage area, and less weight thanks to its technical design. This product introduction is the ideal solution for a wide range of area lighting and recreational sports lighting applications. It incorporates the latest LED light source, one-piece optical system, heat sink and driver into a compact and robust housing that meets globally-recognized safety standards. Its specially-designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, Tango G4 LED floodlights deliver superior performance and a longer lifetime, bringing area lighting to a whole new level.

Warnings and Safety

- please pay attention to the mounting instructions

Product data

General Information		Color rendering index (CRI)		>70
Driver included	Yes	Light source color	757 cool white	
Service tag	Yes	Operating and Electrical		
Lighting Technology	LED	Input Voltage	220 to 240 V	
Value ladder	Performance	Line Frequency	50 or 60 Hz	
Light Technical		Power Consumption	70 W	
Luminous Flux	9,200 lm	Power Factor (Fraction)	0.9	
Correlated Color Temperature (Nom)	5700 K	Connection	Flying leads/wires	
Luminous Efficacy (rated) (Nom)	131 lm/W	Cable	Cable 0.5 m without plug	

Tango G4 LED Flood

Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Gray
Overall length	265 mm
Overall width	419 mm
Overall height	79 mm
Dimensions (Height x Width x Depth)	79 x 419 x 265 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	4.430 kg

Approval and Application	
CE mark	Yes
Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP431 LED92/CW 220~240V 70W SWB GC
Full product name	BVP431 LED92/CW 220~240V 70W SWB GC
Order code	911401680706
Material Nr. (12NC)	911401680706
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

