



# Uni Posttop

## BDS400 LED NW 220V 60W WB PSU 7012

Uni Posttop, 8400 lm, 60 W, 740 neutral white, Safety class I

The modern shaped post top attracts customers' attention with its unique, streamlined design. The fixture distributes soft and homogeneous light to pathways, residential areas thanks to the application of the reflector. Various quality test based on Philips standards offers robustness not only to its design but also functionality, delivering table and outstanding performance to customers.

### Product data

General Information		Protection class IEC	Safety class I
Driver included	Yes	<b>Controls and Dimming</b>	
Light source engine type	LED	Dimmable	No
Warranty period	3 years	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	8,400 lm	Housing Material	Aluminum die-cast
Correlated Color Temperature (Nom)	4000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	130 lm/W	Housing Color	Gray
Color rendering index (CRI)	70	Overall length	722 mm
Light source color	740 neutral white	Overall width	722 mm
<b>Operating and Electrical</b>		Overall height	522 mm
Input Voltage	220 to 240 V	Dimensions (Height x Width x Depth)	522 x 722 x 722 mm
Line Frequency	50 or 60 Hz	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Power Consumption	60 W	Mech. impact protection code	IK08 [5 J vandal-protected]
Power Factor (Fraction)	0.95	Optical cover type	Polycarbonate bowl/cover clear
Connection	Connection unit 3-pole	Net Weight (Piece)	7.790 kg
Cable	Cable 1.0 m without plug		

# Uni Posttop

## Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	BDS400 LED NW 220V 60W WB PSU 7012
--------------------	------------------------------------

Full product name	BDS400 LED NW 220V 60W WB PSU 7012
Full product code	692382861107100
Order code	911401696608
Material Nr. (12NC)	911401696608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828611071
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828611071

## Dimensional drawing

