Uni Wall Sconce

BWP410 LED NW 220V 40W NB PSU 7012

Uni Wall Sconce, 5400 lm, 40 W, 740 neutral white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Warranty period	3 years

Light Technical	
Luminous Flux	5,400 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	40 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable without plug
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Control interface	-

Uni Wall Sconce

Mechanical and Housing	
Housing Material	Aluminum die-cast
Optical cover material	Tempered glass
Housing Color	Gray
Overall length	222 mm
Overall width	150 mm
Overall height	359 mm
Dimensions (Height x Width x Depth)	359 x 150 x 222 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	4.190 kg

Approval and Application	
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BWP410 LED NW 220V 40W NB PSU 7012
Full product name	BWP410 LED NW 220V 40W NB PSU 7012
Full product code	692382861085299
Order code	911401697008
Material Nr. (12NC)	911401697008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610852
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828611125

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.