



Uni Wall Sconce

BWP411 LED WW 220V 40W NB PSU 7012

Uni Wall Sconce, 5000 lm, 40 W, 730 warm white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

Product data

General Information		Line Frequency	
Driver included	Yes	Line Frequency	50 or 60 Hz
Light source engine type	LED	Power Consumption	40 W
Value ladder	Performance	Power Factor (Fraction)	0.95
Warranty period	3 years	Connection	Connection unit 3-pole
		Cable	Cable without plug
		Protection class IEC	Safety class I
Light Technical		Controls and Dimming	
Luminous Flux	5,000 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	125 lm/W		
Color rendering index (CRI)	70	Mechanical and Housing	
Light source color	730 warm white	Housing Material	Aluminum die-cast
		Optical cover material	Tempered glass
Operating and Electrical		Housing Color	Gray
Input Voltage	220 to 240 V		

Uni Wall Sconce

Overall length	204 mm
Overall width	140 mm
Overall height	359 mm
Dimensions (Height x Width x Depth)	359 x 140 x 204 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	2.690 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	BWP411 LED WW 220V 40W NB PSU 7012
Full product name	BWP411 LED WW 220V 40W NB PSU 7012
Full product code	692382861088399
Order code	911401697308
Material Nr. (12NC)	911401697308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610883
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828611156

Dimensional drawing

