Uni Wall Sconce

BWP411 LED WW 220V 40W MB PSU 7012

Uni Wall Sconce, 5000 lm, 40 W, 730 warm white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g. parking areas, entrances, outdoor terrace and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with each scenario, delivering the optimised lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy-efficient and stable choice in the existing wall mounting family.

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Warranty period	3 years

Light Technical	
Luminous Flux	5,000 lm
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	125 lm/W
Colour rendering index (CRI)	70
Light source colour	730 warm white

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	40 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable without plug
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing material	Aluminium die-cast
Optical cover/lens material	Tempered glass
Housing Colour	Grey

Uni Wall Sconce

Overall length	204 mm
Overall width	140 mm
Overall height	359 mm
Dimensions (height x width x depth)	359 x 140 x 204 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	2.690 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BWP411 LED WW 220V 40W MB PSU 7012
Full product name	BWP411 LED WW 220V 40W MB PSU 7012
Full EOC	692382861089099
Order code	911401697408
Material no. (12 NC)	911401697408
Numerator – quantity per pack	1
EAN/UPC — Product/Case	6923828610890
Numerator – packs per outer box	4
EAN/UPC - Case	6923828611163

Dimensional drawing



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.