



# Uni Wall Sconce

## BWP411 LED NW 220V 40W MB PSU 7012

Uni Wall Sconce, 5400 lm, 40 W, 740 neutral white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

### Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
Value ladder	Performance	Power Consumption	40 W
Warranty period	3 years	Power Factor (Fraction)	0.95
Light Technical		Connection	Connection unit 3-pole
Luminous Flux	5,400 lm	Cable	Cable without plug
Correlated Color Temperature (Nom)	4000 K	Protection class IEC	Safety class I
Luminous Efficacy (rated) (Nom)	125 lm/W	Controls and Dimming	
Color rendering index (CRI)	70	Dimmable	No
Light source color	740 neutral white	Control interface	-

# Uni Wall Sconce

## Mechanical and Housing

Housing Material	Aluminum die-cast
Optical cover material	Tempered glass
Housing Color	Gray
Overall length	204 mm
Overall width	140 mm
Overall height	359 mm
Dimensions (Height x Width x Depth)	359 x 140 x 204 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	2.690 kg

## Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	BWP411 LED NW 220V 40W MB PSU 7012
Full product name	BWP411 LED NW 220V 40W MB PSU 7012
Full product code	692382861093799
Order code	911401697708
Material Nr. (12NC)	911401697708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610937
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828611194

## Dimensional drawing

