



Uni Wall Mount

BWP420 LED NW 220V 20W WB PSU 7012

Uni Wall Mount, 2700 lm, 20 W, 740 neutral white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. Thanks to the adjustable mounting angle, the fixture can be installed in accordance with per requirement, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount help you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount offers an affordable, energy – efficient and stable choice in wall Mounting family.

Product data

General Information		Line Frequency	
Driver included	Yes	Line Frequency	50 or 60 Hz
Light source engine type	LED	Power Consumption	20 W
Value ladder	Performance	Power Factor (Fraction)	0.95
Warranty period	3 years	Connection	Connection unit 3-pole
Light Technical		Cable	Cable without plug
Luminous Flux	2,700 lm	Protection class IEC	Safety class I
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	125 lm/W	Dimmable	No
Color rendering index (CRI)	70	Control interface	-
Light source color	740 neutral white	Mechanical and Housing	
Operating and Electrical		Housing Material	Aluminum die-cast
Input Voltage	220 to 240 V	Optical cover material	Tempered glass
		Housing Color	Gray

Uni Wall Mount

Overall length	168 mm
Overall width	113 mm
Overall height	197 mm
Dimensions (Height x Width x Depth)	197 x 113 x 168 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	1.390 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	BWP420 LED NW 220V 20W WB PSU 7012
Full product name	BWP420 LED NW 220V 20W WB PSU 7012
Full product code	692382861096899
Order code	911401698008
Material Nr. (12NC)	911401698008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610968
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828611231

Dimensional drawing

