



Uni Wall Mount

BWP421 LED WW 220V 60W WB PSU 7012

Uni Wall Mount, 7500 lm, 60 W, 730 warm white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. Thanks to the adjustable mounting angle, the fixture can be installed in accordance with per requirement, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount help you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount offers an affordable, energy – efficient and stable choice in wall Mounting family.

Product data

General Information		Line Frequency	
Driver included	Yes	Line Frequency	50 or 60 Hz
Light source engine type	LED	Power Consumption	60 W
Value ladder	Performance	Power Factor (Fraction)	0.95
Warranty period	3 years	Connection	Connection unit 3-pole
		Cable	Cable without plug
		Protection class IEC	Safety class I
Light Technical		Controls and Dimming	
Luminous Flux	7,500 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	125 lm/W		
Color rendering index (CRI)	70	Mechanical and Housing	
Light source color	730 warm white	Housing Material	Aluminum die-cast
		Optical cover material	Tempered glass
Operating and Electrical		Housing Color	Gray
Input Voltage	220 to 240 V		

Uni Wall Mount

Overall length	144 mm
Overall width	242 mm
Overall height	287 mm
Dimensions (Height x Width x Depth)	287 x 242 x 144 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	3.090 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	BWP421 LED WW 220V 60W WB PSU 7012
Full product name	BWP421 LED WW 220V 60W WB PSU 7012
Full product code	692382861099999
Order code	911401698308
Material Nr. (12NC)	911401698308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610999
Numerator - Packs per outer box	2
EAN/UPC - Case	6923828611262

Dimensional drawing

