



Uni Wall Mount Recessed

BWP400 LED NW 220V 12W WB PSU 7012

Uni Wall Mount Recessed, 620 lm, 12 W, 740 neutral white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount recessed can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount recessed help you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount recessed offers another affordable, energy – efficient and stable choice in wall Mounting family.

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Warranty period	3 years
Light Technical	
Luminous Flux	620 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	48 lm/W
Color rendering index (CRI)	70

Light source color	740 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	12 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable without plug
Protection class IEC	Safety class I

Uni Wall Mount Recessed

Controls and Dimming

Dimmable	No
Control interface	-

Mechanical and Housing

Housing Material	Aluminum die-cast
Optical cover material	Tempered glass
Housing Color	Gray
Overall length	205 mm
Overall width	107 mm
Overall height	71 mm
Dimensions (Height x Width x Depth)	71 x 107 x 205 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	0.890 kg

Approval and Application

CE mark	Yes
---------	-----

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BWP400 LED NW 220V 12W WB PSU 7012
Full product name	BWP400 LED NW 220V 12W WB PSU 7012
Full product code	692382861103399
Order code	911401698608
Material Nr. (12NC)	911401698608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828611033
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828611293

Dimensional drawing

