



Essential Smartbright T5 Batten

BN058C LED3/CW L300

Essential Smartbright T5 Batten, 3.4 W, 300 lm, 6500 K

BN058 Batten provide flexibility to customer to choose from 3 CCT and 4 different size and lumen packages, based on their specific need.

Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
Value ladder	Value	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	300 lm	Housing Material	Polycarbonate
Correlated Color Temperature (Nom)	6500 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	85 lm/W	Housing Color	White
Color rendering index (CRI)	>70	Optical cover finish	Opal
Light source color	765 cool daylight	Overall length	325 mm
		Overall width	21 mm
		Overall height	32.3 mm
Operating and Electrical		Dimensions (Height x Width x Depth)	32 x 21 x 325 mm
Input Voltage	220 to 240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK02 [0.2 J standard]
Power Consumption	3.4 W	Optical cover type	Polycarbonate
Power Factor (Fraction)	0.45	Net Weight (Piece)	0.050 kg
Number of products on MCB of 16 A type B	8		
Protection class IEC	Safety class II	Approval and Application	
		CE mark	No

Essential Smartbright T5 Batten

Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BN058C LED3/CW L300
Full product name	BN058C LED3/CW L300

Full product code	911401709242
Order code	911401709242
Material Nr. (12NC)	911401709242
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828624750
Numerator - Packs per outer box	24
EAN/UPC - Case	6923828624996

