



Essential Smartbright T5 Batten

BN058C LED11/WW L1200 GM

Essential Smartbright T5 Batten, 13 W, 1200 lm, 3000 K

BN058 Batten provide flexibility to customer to choose from 3 CCT and 4 different size and lumen packages, based on their specific need.

Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
Value ladder	Value	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	1,200 lm	Housing Material	Polycarbonate
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	85 lm/W	Housing Color	White
Color rendering index (CRI)	>70	Optical cover finish	Opal
Light source color	730 warm white	Overall length	1,185 mm
Operating and Electrical		Overall width	21 mm
Input Voltage	220 to 240 V	Overall height	32.3 mm
Line Frequency	50 or 60 Hz	Dimensions (Height x Width x Depth)	32 x 21 x 1185 mm
Power Consumption	13 W	Ingress protection code	IP20 [Finger-protected]
Power Factor (Fraction)	0.5	Mech. impact protection code	IK02 [0.2 J standard]
Number of products on MCB of 16 A type B	8	Optical cover type	Polycarbonate
Protection class IEC	Safety class II	Net Weight (Piece)	0.120 kg
		Approval and Application	
		CE mark	No

Essential Smartbright T5 Batten

Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BN058C LED11/WW L1200 GM
Full product name	BN058C LED11/WW L1200 GM

Full product code	871016331394899
Order code	31394899
Material Nr. (12NC)	911401709522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163313948
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163314181

