



Essential Smartbright T5 Batten

BN058C LED3/NW L300 GM

Essential Smartbright T5 Batten, 3.4 W, 300 lm, 4000 K

BN058 Batten provide flexibility to customer to choose from 3 CCT and 4 different size and lumen packages, based on their specific need.

Product data

| General Information | | Controls and Dimming | |
|--|-------------------|-------------------------------------|-------------------------|
| Light source engine type | LED | Dimmable | No |
| Value ladder | Value | Control interface | - |
| Light Technical | | Mechanical and Housing | |
| Luminous Flux | 300 lm | Housing Material | Polycarbonate |
| Correlated Color Temperature (Nom) | 4000 K | Optical cover material | Polycarbonate |
| Luminous Efficacy (rated) (Nom) | 85 lm/W | Housing Color | White |
| Color rendering index (CRI) | >70 | Optical cover finish | Opal |
| Light source color | 740 neutral white | Overall length | 325 mm |
| Operating and Electrical | | Overall width | 21 mm |
| Input Voltage | 220 to 240 V | Overall height | 32.3 mm |
| Line Frequency | 50 or 60 Hz | Dimensions (Height x Width x Depth) | 32 x 21 x 325 mm |
| Power Consumption | 3.4 W | Ingress protection code | IP20 [Finger-protected] |
| Power Factor (Fraction) | 0.45 | Mech. impact protection code | IK02 [0.2 J standard] |
| Number of products on MCB of 16 A type B | 8 | Optical cover type | Polycarbonate |
| Protection class IEC | Safety class II | Net Weight (Piece) | 0.050 kg |
| Approval and Application | | | |
| CE mark | No | | |

Essential Smartbright T5 Batten

| | |
|--|------------------------|
| Ambient temperature range | -20 to +40 °C |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |
| Product Data | |
| Order product name | BN058C LED3/NW L300 GM |
| Full product name | BN058C LED3/NW L300 GM |

| | |
|---------------------------------|-----------------|
| Full product code | 871016331404499 |
| Order code | 911401709622 |
| Material Nr. (12NC) | 911401709622 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163314044 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 8710163314280 |

