



GreenSpace Flex

RS378Z M55 D78 R-R FX D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information	
Light source engine type	-
Value ladder	Performance
Warranty period	3 years

Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Beam angle of light source	- degree(s)
Light source color	-
Optic type	-

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-
Number of products on MCB of 16 A type B	-
Protection class IEC	-

Controls and Dimming	
Control interface	-

Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	42 mm
Overall diameter	85 mm
Dimensions (Height x Width x Depth)	42 x 0 x 0 mm
Material	Aluminum
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Accessory color	White
Optical cover type	-
Net Weight (Piece)	0.110 kg

Greenspace Flex

Approval and Application





Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	-
CE mark	No
ENEC mark	-
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	RS378Z M55 D78 R-R FX D
Full product name	RS378Z M55 D78 R-R FX D

Full product code	692382865958599
Order code	911401721712
Material Nr. (12NC)	911401721712
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828659585
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828659622

Dimensional drawing



Cut out: Ø78

