



GreenSpace Flex

RS378Z M55 D78 S-S AJ D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Constant light output	
Light source engine type	-	Constant light output	No
Value ladder	Performance	Maximum dim level	Not applicable
Warranty period	3 years		
Light Technical		Mechanical and Housing	
Correlated Color Temperature (Nom)	-	Housing Material	Aluminum
Color rendering index (CRI)	-	Optical cover material	-
Beam angle of light source	- degree(s)	Fixation material	Aluminum
Light source color	-	Housing Color	White
Optic type	-	Optical cover finish	-
		Overall length	85 mm
		Overall width	85 mm
		Overall height	52 mm
		Overall diameter	0 mm
Operating and Electrical		Dimensions (Height x Width x Depth)	52 x 85 x 85 mm
Input Voltage	- V	Material	Aluminum
Line Frequency	- Hz	Ingress protection code	IP20 [Finger-protected]
Cable	-	Mech. impact protection code	IK04 [0.5 J standard plus]
Number of products on MCB of 16 A type B	-	Accessory color	White
Protection class IEC	-	Optical cover type	-
		Net Weight (Piece)	0.120 kg
Controls and Dimming			
Control interface	-		

Greenspace Flex

Approval and Application

Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	-
CE mark	No
ENEC mark	-
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	RS378Z M55 D78 S-S AJ D
--------------------	-------------------------

Full product name	RS378Z M55 D78 S-S AJ D
Full product code	911401721722
Order code	911401721722
Material Nr. (12NC)	911401721722
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

Dimensional drawing

