



# GreenSpace Flex

## RS378Z M55 D78 S-S AJ D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information		Constant light output	
Light source engine type	-	Constant light output	No
Value ladder	Performance	Maximum dim level	Not applicable
Warranty period	3 years	<b>Mechanical and Housing</b>	
Light Technical		Housing Material	Aluminum
Correlated Color Temperature (Nom)	-	Optical cover material	-
Color rendering index (CRI)	-	Fixation material	Aluminum
Beam angle of light source	- degree(s)	Housing Color	White
Light source color	-	Optical cover finish	-
Optic type	-	Overall length	85 mm
Operating and Electrical		Overall width	85 mm
Input Voltage	- V	Overall height	52 mm
Line Frequency	- Hz	Overall diameter	0 mm
Cable	-	Dimensions (Height x Width x Depth)	52 x 85 x 85 mm
Number of products on MCB of 16 A type B	-	Material	Aluminum
Protection class IEC	-	Ingress protection code	IP20 [Finger-protected]
Controls and Dimming		Mech. impact protection code	IK04 [0.5 J standard plus]
Control interface	-	Accessory color	White
		Optical cover type	-
		Net Weight (Piece)	0.120 kg

# Greenspace Flex

## Approval and Application

Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	-
CE mark	No
ENEC mark	-
Ambient temperature range	-20 to +45 °C

## Product Data

Order product name	RS378Z M55 D78 S-S AJ D
--------------------	-------------------------

Full product name	RS378Z M55 D78 S-S AJ D
Full product code	911401721722
Order code	911401721722
Material Nr. (12NC)	911401721722
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

## Dimensional drawing

