



Greenspace Flex

RS378Z M55 D92 R-R FX D

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data





General Information		Maximum dim level		Not applicable
Light source engine type	-			
Value ladder	Performance	Mechanical and Housing		
Warranty period	3 years	Housing Material		Aluminum
Light Technical		Optical cover material		-
Correlated Color Temperature (Nom)	-	Fixation material		Aluminum
Color rendering index (CRI)	-	Housing Color		White
Light source color	-	Optical cover finish		-
Operating and Electrical		Overall length		0 mm
Input Voltage	- V	Overall width		0 mm
Line Frequency	- Hz	Overall height		48 mm
Cable	-	Overall diameter		105 mm
Number of products on MCB of 16 A type B	-	Dimensions (Height x Width x Depth)		48 x 0 x 0 mm
Protection class IEC	-	Material		Aluminum
Controls and Dimming		Ingress protection code		IP20 [Finger-protected]
Control interface	-	Mech. impact protection code		IK04 [0.5 J standard plus]
Constant light output	No	Accessory color		White
		Optical cover type		-
		Net Weight (Piece)		0.160 kg

Greenspace Flex

Approval and Application	
CE mark	No
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	RS378Z M55 D92 R-R FX D
Full product name	RS378Z M55 D92 R-R FX D

Full product code	911401721742
Order code	911401721742
Material Nr. (12NC)	911401721742
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

Dimensional drawing



Cut out: Ø92

