



GreenSpace Flex

RS378Z M55 D102 R-R AJ D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Maximum dim level	Not applicable
Light source engine type	-	Mechanical and Housing	
Value ladder	Performance	Housing Material	Aluminum
Warranty period	3 years	Optical cover material	-
Light Technical		Fixation material	Aluminum
Correlated Color Temperature (Nom)	-	Housing Color	White
Color rendering index (CRI)	-	Optical cover finish	-
Light source color	-	Overall length	0 mm
Operating and Electrical		Overall width	0 mm
Input Voltage	- V	Overall height	62 mm
Line Frequency	- Hz	Overall diameter	115 mm
Cable	-	Dimensions (Height x Width x Depth)	62 x 0 x 0 mm
Number of products on MCB of 16 A type B	-	Material	Aluminum
Protection class IEC	-	Ingress protection code	IP20 [Finger-protected]
Controls and Dimming		Mech. impact protection code	IK04 [0.5 J standard plus]
Control interface	-	Accessory color	White
Constant light output	No	Optical cover type	-
		Net Weight (Piece)	0.190 kg

Greenspace Flex

Approval and Application

CE mark	No
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	RS378Z M55 D102 R-R AJ D
Full product name	RS378Z M55 D102 R-R AJ D

Full product code	911401721752
Order code	911401721752
Material Nr. (12NC)	911401721752
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

Dimensional drawing

