



# GreenSpace Flex

## RS378Z M55 D102 R-R FX D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

| General Information                      |             | Maximum dim level                   | Not applicable             |
|--|-------------|-------------------------------------|----------------------------|
| Light source engine type                 | -           | Mechanical and Housing              |                            |
| Value ladder                             | Performance | Housing Material                    | Aluminum                   |
| Warranty period                          | 3 years     | Optical cover material              | -                          |
| Light Technical                          |             | Fixation material                   | Aluminum                   |
| Correlated Color Temperature (Nom)       | -           | Housing Color                       | White                      |
| Color rendering index (CRI)              | -           | Optical cover finish                | -                          |
| Light source color                       | -           | Overall length                      | 0 mm                       |
| Operating and Electrical                 |             | Overall width                       | 0 mm                       |
| Input Voltage                            | - V         | Overall height                      | 52 mm                      |
| Line Frequency                           | - Hz        | Overall diameter                    | 115 mm                     |
| Cable                                    | -           | Dimensions (Height x Width x Depth) | 52 x 0 x 0 mm              |
| Number of products on MCB of 16 A type B | -           | Material                            | Aluminum                   |
| Protection class IEC                     | -           | Ingress protection code             | IP20 [Finger-protected]    |
| Controls and Dimming                     |             | Mech. impact protection code        | IK04 [0.5 J standard plus] |
| Control interface                        | -           | Accessory color                     | White                      |
| Constant light output                    | No          | Optical cover type                  | -                          |
|  |             | Net Weight (Piece)                  | 0.190 kg                   |

# Greenspace Flex

## Approval and Application

|                           |               |
|---------------------------|---------------|
| CE mark                   | No            |
| Ambient temperature range | -20 to +45 °C |

## Product Data

|                    |                          |
|--------------------|--------------------------|
| Order product name | RS378Z M55 D102 R-R FX D |
| Full product name  | RS378Z M55 D102 R-R FX D |

|                                 |              |
|---------------------------------|--------------|
| Full product code               | 911401721762 |
| Order code                      | 01721762     |
| Material Nr. (12NC)             | 911401721762 |
| Numerator - Quantity Per Pack   | 1            |
| Numerator - Packs per outer box | 36           |

## Dimensional drawing

