



Greenspace Flex

RS378Z M55 D102 R-R FX D

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Maximum dim level	
Light source engine type	-	Not applicable	
Value ladder	Performance	Mechanical and Housing	
Warranty period	3 years	Housing Material	Aluminum
Light Technical		Optical cover material	-
Correlated Color Temperature (Nom)	-	Fixation material	Aluminum
Color rendering index (CRI)	-	Housing Color	White
Light source color	-	Optical cover finish	-
Operating and Electrical		Overall length	0 mm
Input Voltage	- V	Overall width	0 mm
Line Frequency	- Hz	Overall height	52 mm
Cable	-	Overall diameter	115 mm
Number of products on MCB of 16 A type B	-	Dimensions (Height x Width x Depth)	52 x 0 x 0 mm
Protection class IEC	-	Material	Aluminum
Controls and Dimming		Ingress protection code	IP20 [Finger-protected]
Control interface	-	Mech. impact protection code	IK04 [0.5 J standard plus]
Constant light output	No	Accessory color	White
		Optical cover type	-
		Net Weight (Piece)	0.190 kg

Greenspace Flex

Approval and Application

CE mark	No
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	RS378Z M55 D102 R-R FX D
Full product name	RS378Z M55 D102 R-R FX D

Full product code	911401721762
Order code	911401721762
Material Nr. (12NC)	911401721762
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

Dimensional drawing

