



GreenSpace Flex

RS378Z M55 D75 R-R FX

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Maximum dim level		Not applicable
Light source engine type	-			
Value ladder	Performance	Mechanical and Housing		
Warranty period	3 years	Housing Material	Aluminum	
Light Technical		Optical cover material	-	
Correlated Color Temperature (Nom)	-	Fixation material	Aluminum	
Color rendering index (CRI)	-	Housing Color	White	
Light source color	-	Optical cover finish	-	
Operating and Electrical		Overall length	0 mm	
Input Voltage	- V	Overall width	0 mm	
Line Frequency	- Hz	Overall height	30 mm	
Cable	-	Overall diameter	85 mm	
Number of products on MCB of 16 A type B	-	Dimensions (Height x Width x Depth)	30 x 0 x 0 mm	
Protection class IEC	-	Material	Aluminum	
Controls and Dimming		Ingress protection code	IP20 [Finger-protected]	
Control interface	-	Mech. impact protection code	IK04 [0.5 J standard plus]	
Constant light output	No	Accessory color	White	
		Optical cover type	-	
		Net Weight (Piece)	0.070 kg	

Approval and Application	
CE mark	No
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	RS378Z M55 D75 R-R FX
Full product name	RS378Z M55 D75 R-R FX
Full product code	872016953212099

Order code	911401721782
Material Nr. (12NC)	911401721782
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532120
Numerator - Packs per outer box	96
EAN/UPC - Case	8720169543614

Dimensional drawing

