



# Greenspace Flex

## RS378Z M55 D75 R-R AJ

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information		Mechanical and Housing	
Light source engine type	-	Maximum dim level	Not applicable
Value ladder	Performance	Housing Material	Aluminum
Warranty period	3 years	Optical cover material	-
Light Technical		Fixation material	Aluminum
Correlated Color Temperature (Nom)	-	Housing Color	White
Color rendering index (CRI)	-	Optical cover finish	-
Light source color	-	Overall length	0 mm
Operating and Electrical		Overall width	0 mm
Input Voltage	- V	Overall height	17 mm
Line Frequency	- Hz	Overall diameter	85 mm
Cable	-	Dimensions (Height x Width x Depth)	17 x 0 x 0 mm
Number of products on MCB of 16 A type B	-	Material	Aluminum
Protection class IEC	-	Ingress protection code	IP20 [Finger-protected]
Controls and Dimming		Mech. impact protection code	IK04 [0.5 J standard plus]
Control interface	-	Accessory color	White
Constant light output	No	Optical cover type	-
		Net Weight (Piece)	0.070 kg

# Greenspace Flex

## Approval and Application



CE mark	No
Ambient temperature range	-20 to +45 °C

## Product Data

Order product name	RS378Z M55 D75 R-R AJ
Full product name	RS378Z M55 D75 R-R AJ

Full product code	911401721792
Order code	01721792
Material Nr. (12NC)	911401721792
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

## Dimensional drawing



Cut out: Ø75

