

Greenspace Flex

RS378Z M55 D75 R-R FX PH WP

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Maximum dim level	Not applicable
Light source engine type	-	Mechanical and Housing	
Value ladder	Performance	Housing Material	Aluminum
Warranty period	3 years	Optical cover material	-
Light Technical		Fixation material	Aluminum
Correlated Color Temperature (Nom)	-	Housing Color	White
Color rendering index (CRI)	-	Optical cover finish	-
Light source color	-	Overall length	0 mm
Operating and Electrical		Overall width	0 mm
Input Voltage	- V	Overall height	48 mm
Line Frequency	- Hz	Overall diameter	88 mm
Cable	-	Dimensions (Height x Width x Depth)	48 x 0 x 0 mm
Number of products on MCB of 16 A type B	-	Material	Aluminum
Protection class IEC	-	Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Controls and Dimming		Mech. impact protection code	IK04 [0.5 J standard plus]
Control interface	-	Accessory color	White
Constant light output	No	Optical cover type	-
		Net Weight (Piece)	0.130 kg

Greenspace Flex

Approval and Application





CE mark	No
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	RS378Z M55 D75 R-R FX PH WP
Full product name	RS378Z M55 D75 R-R FX PH WP
Full product code	692382865957899

Order code	911401721852
Material Nr. (12NC)	911401721852
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828659578
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828659615

Dimensional drawing



Cut out: Ø75

