

Greenspace Flex

RS378Z M55 D75 R-R FX PH WP

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information	
Light source engine type	-
Value ladder	Performance
Warranty period	3 years
Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Light source color	-
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-
Number of products on MCB of 16 A type B	-
Protection class IEC	-
Controls and Dimming	
Control interface	-
Constant light output	No

Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	48 mm
Overall diameter	88 mm
Dimensions (Height x Width x Depth)	48 x 0 x 0 mm
Material	Aluminum
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK04 [0.5 J standard plus]
Accessory color	White
Optical cover type	-
Net Weight (Piece)	0.130 kg

Greenspace Flex

Approval and Application





CE mark	No
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	RS378Z M55 D75 R-R FX PH WP
Full product name	RS378Z M55 D75 R-R FX PH WP
Full product code	692382865957899

Order code	911401721852
Material Nr. (12NC)	911401721852
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828659578
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828659615

Dimensional drawing



Cut out: Ø75

