



Greenspace Flex

RS378Z M55 D75 R-R FX PH WP

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.



Product data

General Information		Maximum dim level		Not applicable
Light source engine type	-			
Value ladder	Performance			
Warranty period	3 years			
Light Technical		Mechanical and Housing		
Correlated Color Temperature (Nom)	-	Housing Material	Aluminum	
Color rendering index (CRI)	-	Optical cover material	-	
Light source color	-	Fixation material	Aluminum	
		Housing Color	White	
		Optical cover finish	-	
		Overall length	0 mm	
		Overall width	0 mm	
		Overall height	48 mm	
		Overall diameter	88 mm	
		Dimensions (Height x Width x Depth)	48 x 0 x 0 mm	
		Material	Aluminum	
		Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]	
		Mech. impact protection code	IK04 [0.5 J standard plus]	
		Accessory color	White	
		Optical cover type	-	
		Net Weight (Piece)	0.130 kg	

Approval and Application	
CE mark	No
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	RS378Z M55 D75 R-R FX PH WP
Full product name	RS378Z M55 D75 R-R FX PH WP
Full product code	692382865957899

Order code	911401721852
Material Nr. (12NC)	911401721852
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828659578
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828659615

Dimensional drawing



Cut out: Ø75

