



# GreenSpace Flex

## RS378Z M102 D150 R-R AJ

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information	
Light source engine type	-
Value ladder	Performance
Warranty period	3 years
Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Light source color	-
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-
Number of products on MCB of 16 A type B	-
Protection class IEC	-
Controls and Dimming	
Control interface	-
Constant light output	No

Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	54 mm
Overall diameter	165 mm
Dimensions (Height x Width x Depth)	54 x 0 x 0 mm
Material	Aluminum
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Accessory color	White
Optical cover type	-
Net Weight (Piece)	0.430 kg

# Greenspace Flex

## Approval and Application


CE mark	No
Ambient temperature range	-20 to +45 °C

## Product Data

Order product name	RS378Z M102 D150 R-R AJ
Full product name	RS378Z M102 D150 R-R AJ

Full product code	911401722122
Order code	911401722122
Material Nr. (12NC)	911401722122
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

## Dimensional drawing



Cut out: Ø150

