



# GreenSpace Flex

## RS378Z M102 D150 R-R AJ

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information		Maximum dim level	
Light source engine type	-	Not applicable	
Value ladder	Performance	Mechanical and Housing	
Warranty period	3 years	Housing Material	Aluminum
Light Technical		Optical cover material	-
Correlated Color Temperature (Nom)	-	Fixation material	Aluminum
Color rendering index (CRI)	-	Housing Color	White
Light source color	-	Optical cover finish	-
Operating and Electrical		Overall length	0 mm
Input Voltage	- V	Overall width	0 mm
Line Frequency	- Hz	Overall height	54 mm
Cable	-	Overall diameter	165 mm
Number of products on MCB of 16 A type B	-	Dimensions (Height x Width x Depth)	54 x 0 x 0 mm
Protection class IEC	-	Material	Aluminum
Controls and Dimming		Ingress protection code	IP20 [Finger-protected]
Control interface	-	Mech. impact protection code	IK04 [0.5 J standard plus]
Constant light output	No	Accessory color	White
		Optical cover type	-
		Net Weight (Piece)	0.430 kg

# Greenspace Flex

## Approval and Application


CE mark	No
Ambient temperature range	-20 to +45 °C

## Product Data

Order product name	RS378Z M102 D150 R-R AJ
Full product name	RS378Z M102 D150 R-R AJ

Full product code	911401722122
Order code	911401722122
Material Nr. (12NC)	911401722122
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

## Dimensional drawing



Cut out: Ø150

