



# UNIUrban

## BGP461 LED120 NW 110-277V TS

UNIUrban, 12000 lm, 100 W, Neutral white, Safety class I, Side-entry for diameter 60 mm

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

### Product data

General Information	
Light source replaceable	No
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	12,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	≥70
Light source color	Neutral white
Operating and Electrical	
Input Voltage	110 to 277 V
Line Frequency	50 to 60 Hz
Power Consumption	100 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug

Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	Tempered glass
Housing Color	Grey
Mounting device	Side-entry for diameter 60 mm
Optical cover finish	Clear
Overall length	691 mm
Overall width	480 mm
Overall height	66 mm
Overall diameter	488 mm
Dimensions (Height x Width x Depth)	66 x 480 x 691 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Standard tilt angle posttop	15°
Optical cover type	Polycarbonate micro lens optic
Net Weight (Piece)	10.649 kg

### Approval and Application

Flammability mark	-
CE mark	Yes
Ambient temperature range	-40 to +50 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Sustainability Data

Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician.
--------------	--

Parts and documentation are available for an extended period of time.

### Product Data

Order product name	BGP461 LED120 NW 110-277V TS
Full product name	BGP461 LED120 NW 110-277V TS
Full product code	911401727592
Order code	911401727592
Material Nr. (12NC)	911401727592
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

### Dimensional drawing

