



UNIUrban

BSP461 LED78 WW 110-277V TA

UNIUrban, 7800 lm, 65 W, Warm white, Safety class I, Catenary pole 35mm with Ø 10mm hole

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

Product data

General Information		Protection class IEC	
Light source replaceable	No	Safety class I	
Driver included	Yes	Controls and Dimming	
Light source engine type	LED	Dimmable	No
Value ladder	Performance	Control interface	-
Light Technical		Constant light output	No
Luminous Flux	7,800 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Housing Material	Aluminum
Luminous Efficacy (rated) (Nom)	120 lm/W	Optical cover material	Tempered glass
Color rendering index (CRI)	≥70	Housing Color	Grey
Light source color	Warm white	Mounting device	Catenary pole 35mm with Ø 10mm hole
Operating and Electrical		Optical cover finish	Clear
Input Voltage	110 to 277 V	Overall height	112 mm
Line Frequency	50 to 60 Hz	Overall diameter	482 mm
Power Consumption	65 W	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Power Factor (Fraction)	0.95	Mech. impact protection code	IK08 [5 J vandal-protected]
Connection	Flying leads/wires	Standard tilt angle posttop	-
Cable	Cable 0.6 m without plug	Optical cover type	Polycarbonate micro lens optic

Net Weight (Piece)	8.999 kg
--------------------	----------

Approval and Application

Flammability mark	-
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Sustainability Data

Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician.
--------------	--

Parts and documentation are available for an extended period of time.

Product Data

Order product name	BSP461 LED78 WW 110-277V TA
Full product name	BSP461 LED78 WW 110-277V TA
Full product code	911401727682
Order code	911401727682
Material Nr. (12NC)	911401727682
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

