



# UniSpot

## BVP378 4LED RGB30K 220V 15 RDM 50W

UniSpot, 1520 lm, 50 W, Red, green, blue and white, DMX, Safety class I

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

### Product data

General Information	
Driver included	Yes
Light Technical	
Luminous Flux	1,520 lm
Correlated Color Temperature (Nom)	RGBW
Luminous Efficacy (rated) (Nom)	30 lm/W
Color rendering index (CRI)	>80
Light source color	Red, green, blue and white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	50 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires and 2 Push-in connector 4-pole

Cable	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Control interface	DMX
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Glass
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	2.850 kg

## Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	BVP378 4LED RGB30K 220V 15 RDM 50W
--------------------	------------------------------------

Full product name	BVP378 4LED RGB30K 220V 15 RDM 50W
Full product code	872110370307199
Order code	911401733614
Material Nr. (12NC)	911401733614
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103703071
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103703071

## Dimensional drawing

