PHILIPS

BVP378 4LED RGB30K 220V 30 RDM 50W

911401733644

UniSpot, 1335 lm, 50 W, Red, green, blue and white, DMX, Safety class I

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobstrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

General Information

Driver included	Yes

Light Technical

Luminous Flux	1,335 lm
Correlated Color Temperature (Nom)	RGBW

Luminous Efficacy (rated) (Nom)	26 lm/W
Color rendering index (CRI)	>80
Light source color	Red, green, blue and white

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	50 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires and 2 Push-in connector 4-pole
Cable	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Control interface	DMX

Mechanical and Housing

Housing Material	Aluminum Alloy
Optical cover material	Glass
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	2.850 kg

Dimensional drawing



Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP378 4LED RGB30K 220V 30 RDM 50W
Full product name	BVP378 4LED RGB30K 220V 30 RDM 50W
Full product code	872110370310199
Order code	70310199
Material Nr. (12NC)	911401733644
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103703101
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103703101

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	UniSpot-BVP378-INI.pdf	Download

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.