PHILIPS

Lighting

# UniSpot

## BVP378 4LED RGB40K 220V 30 RDM 50W

UniSpot, 1405 lm, 50 W, Red, green, blue and white, DMX, Safety class I

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobstrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

### Product data

| General Information | |
|---|---|
| **Driver included** | Yes |

| Light Technical | |
|---|---|
| **Luminous Flux** | 1,405 lm |
| **Correlated Color Temperature (Nom)** | RGBW |
| **Luminous Efficacy (rated) (Nom)** | 28 lm/W |
| **Color rendering index (CRI)** | >80 |
| **Light source color** | Red, green, blue and white |

| Operating and Electrical | |
|---|---|
| **Input Voltage** | 220 to 240 V |
| **Line Frequency** | 50 or 60 Hz |
| **Power Consumption** | 50 W |
| **Power Factor (Fraction)** | 0.9 |
| **Connection** | Flying leads/wires and 2 Push-in connector 4-pole |
| **Cable** | Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole |
| **Protection class IEC** | Safety class I |

| Controls and Dimming | |
|---|---|
| **Dimmable** | Yes |
| **Control interface** | DMX |

| Mechanical and Housing | |
|---|---|
| **Housing Material** | Aluminum Alloy |
| **Optical cover material** | Glass |
| **Housing Color** | Dark gray |
| **Ingress protection code** | IP66 [Dust penetration-protected, jet-proof] |
| **Mech. impact protection code** | IK06 [1 J] |
| **Optical cover type** | Clear glass |
| **Net Weight (Piece)** | 2.850 kg |

# UniSpot

| Approval and Application | |
|---|---|
| **CE mark** | Yes |
| **Ambient temperature range** | -40 to +50 °C |

| Initial Performance (IEC Compliant) | |
|---|---|
| **Luminous flux tolerance** | +/-10% |
| **Power consumption tolerance** | +/-10% |

| Product Data | |
|---|---|
| **Order product name** | BVP378 4LED RGB40K 220V 30 RDM 50W |
| **Full product name** | BVP378 4LED RGB40K 220V 30 RDM 50W |
| **Full product code** | 872110370311899 |
| **Order code** | 911401733654 |
| **Material Nr. (12NC)** | 911401733654 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8721103703118 |
| **Numerator - Packs per outer box** | 6 |
| **EAN/UPC - Case** | 8721103703118 |

## Dimensional drawing



© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.