



# UniSpot

## BVP377 1LED 40K 24V 15 DMX 30W COB

UniSpot, 2230 lm, 30 W, 840 neutral white, DMX, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

### Product data

| General Information                |                                     | Controls and Dimming                |  |
|------------------------------------|-------------------------------------|-------------------------------------|--|
| Driver included                    | No                                  | Dimmable                            | Yes  |
|                                    |                                     | Control interface                   | DMX  |
| Light Technical                    |                                     | Mechanical and Housing              |  |
| Luminous Flux                      | 2,230 lm                            | Housing Material                    | Aluminum Alloy                               |
| Correlated Color Temperature (Nom) | 4000 K                              | Optical cover material              | Glass  |
| Luminous Efficacy (rated) (Nom)    | 74 lm/W                             | Housing Color                       | Dark gray                                    |
| Color rendering index (CRI)        | >80                                 | Ingress protection code             | IP66 [Dust penetration-protected, jet-proof] |
| Light source color                 | 840 neutral white                   | Mech. impact protection code        | IK06 [1 J]                                   |
| Operating and Electrical           |                                     | Optical cover type                  | Clear glass                                  |
| Input Voltage                      | 24 V                                | Net Weight (Piece)                  | 1.800 kg                                     |
| Line Frequency                     | - Hz                                | Approval and Application            |  |
| Power Consumption                  | 30 W                                | CE mark                             | Yes  |
| Power Factor (Fraction)            | -                                   | Ambient temperature range           | -40 to +50 °C                                |
| Connection                         | 2 Push-in connector 5-pole          | Initial Performance (IEC Compliant) |  |
| Cable                              | 2 cables 0.3m with connector 5-pole | Luminous flux tolerance             | +/-10%                                       |
| Protection class IEC               | Safety class III                    |                                     |  |

|                             |                                    |
|-----------------------------|------------------------------------|
| Power consumption tolerance | +/-10%                             |
| <b>Product Data</b>         |                                    |
| Order product name          | BVP377 1LED 40K 24V 15 DMX 30W COB |
| Full product name           | BVP377 1LED 40K 24V 15 DMX 30W COB |
| Full product code           | 872110370275399                    |
| Order code                  | 911401734494                       |

|                                 |               |
|---------------------------------|---------------|
| Material Nr. (12NC)             | 911401734494  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8721103702753 |
| Numerator - Packs per outer box | 8             |
| EAN/UPC - Case                  | 8721103702753 |

## Dimensional drawing

