PHILIPS

Lighting

UniSpot

BVP377 3LED RGB40K 24V 55 DMX 30W

UniSpot, 975 lm, 30 W, Red, green, blue and white, DMX, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobstrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information	
Driver included	No

Light Technical	
Luminous Flux	975 lm
Correlated Color Temperature (Nom)	RGBW
Luminous Efficacy (rated) (Nom)	32 lm/W
Color rendering index (CRI)	>80
Light source color	Red, green, blue and white

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Power Consumption	30 W
Power Factor (Fraction)	-
Connection	2 Push-in connector 5-pole
Cable	2 cables 0.3m with connector 5-pole

Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	Yes
Control interface	DMX

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Glass
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	1.800 kg

Approval and Application	
CE mark	Yes

UniSpot

Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BVP377 3LED RGB40K 24V 55 DMX 30W
Full product name	BVP377 3LED RGB40K 24V 55 DMX 30W

Full product code	872110370290699
Order code	911401734644
Material Nr. (12NC)	911401734644
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702906
Numerator - Packs per outer box	8
EAN/UPC - Case	8721103702906

Dimensional drawing



© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.