



UniEdge

BCP390 4LED 27K 24V 3x90 D3

UniEdge, 118 lm, 10 W, Warm white, Safety class III

UniEdge is a surface-mounted, exterior-rated and compact-sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Driver included	No
Lighting Technology	LED
Value ladder	Performance

Light Technical	
Luminous Flux	118 lm
Correlated Colour Temperature (Nom)	-
Luminous efficacy (rated) (nom.)	11.8 lm/W
Colour rendering index (CRI)	80
Light source colour	Warm white
Effective projected area	0.014 m ²

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Inrush current	70 A

Power Consumption	10 W
Power Factor (Fraction)	1.0
Connection	2 push-in connectors 2-pole
Cable	2 cables 0.3 m with connector 2-pole
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing material	Aluminium die cast
Optical cover/lens material	Polymethyl methacrylate
Housing Colour	Dark grey
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Tempered glass

Net Weight (Piece)	0.799 kg
--------------------	----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	No
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data

Order product name	BCP390 4LED 27K 24V 3x90 D3
Full product name	BCP390 4LED 27K 24V 3x90 D3
Full EOC	871951492350899
Order code	911401737283
Material no. (12 NC)	911401737283
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514923508
Numerator – packs per outer box	24
EAN/UPC – Case	8719514923508

Dimensional drawing

