



UniEdge

BCP390 4LED 30K 24V 3x90 D3

UniEdge, 127 lm, 10 W, Warm white, Safety class III

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Driver included	No
Lighting Technology	LED
Value ladder	Performance

Light Technical	
Luminous Flux	127 lm
Correlated Color Temperature (Nom)	-
Luminous Efficacy (rated) (Nom)	12.7 lm/W
Color rendering index (CRI)	80
Light source color	Warm white
Effective projected area	0.014 m ²

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Inrush current	70 A
Power Consumption	10 W
Power Factor (Fraction)	1.0
Connection	2 Push-in connector 2-pole
Cable	2 cables 0.3m with connector 2-pole
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing

Housing Material	Aluminum die cast
Optical cover material	Polymethyl methacrylate
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Tempered glass
Net Weight (Piece)	0.799 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	No
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data

Order product name	BCP390 4LED 30K 24V 3x90 D3
Full product name	BCP390 4LED 30K 24V 3x90 D3
Full product code	87195149235299
Order code	92352299
Material Nr. (12NC)	911401737303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514923522
Numerator - Packs per outer box	24
EAN/UPC - Case	8719514923522

Dimensional drawing

