



UniStrip G4

ZCP382 L50 glare shield (10 pcs)

Accessory, UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Value ladder	Performance

Mechanical and Housing	
Overall length	500 mm
Overall width	6.1 mm
Overall height	59 mm
Dimensions (Height x Width x Depth)	59 x 6 x 500 mm
Material	Steel
Accessory color	Dark gray
Net Weight (Piece)	0.870 kg

Product Data	
Order product name	ZCP382 L50 glare shield (10 pcs)
Full product name	ZCP382 L50 glare shield (10 pcs)
Full product code	871951494515900
Order code	911401742312
Material Nr. (12NC)	911401742312
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514945159
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514945159

UniStrip G4

Dimensional drawing

