



UniStrip G4

ZCP382 L100 glare shield (10 pcs)

Accessory, UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

Mechanical and Housing		Full product name	ZCP382 L100 glare shield (10 pcs)
Overall length	1,000 mm	Full product code	871951494516600
Overall width	6.1 mm	Order code	911401742322
Overall height	59 mm	Material Nr. (12NC)	911401742322
Dimensions (Height x Width x Depth)	59 x 6 x 1000 mm	Numerator - Quantity Per Pack	1
Material	Steel	EAN/UPC - Product/Case	8719514945166
Accessory color	Dark gray	Numerator - Packs per outer box	1
Net Weight (Piece)	1.740 kg	EAN/UPC - Case	8719514945166
Product Data			
Order product name	ZCP382 L100 glare shield (10 pcs)		

Dimensional drawing

