



Uni DMX controls and accessories

ZXP399 Addressing Kit DMX

Uni DMX controls and accessories, 6 to 24 DC V, IP20 | Finger-protected, Yes, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include a main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6,000 DMX universes. Stand-alone Controller: Fits all medium applications with up to 700 DMX universes. Wiring accessories include leader and jump cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low-power repeater that can amplify the DMX signal for up 100 metres.

Product data

Operating and Electrical		Net Weight (Piece)	
Input Voltage	6 to 24 DC V		0.260 kg
Line Frequency	- Hz	Approval and Application	
Mechanical and Housing		CE mark	Yes
Overall length	122.4 mm	Product Data	
Overall width	88.15 mm	Order product name	ZXP399 Addressing Kit DMX
Overall height	30 mm	Full product name	ZXP399 Addressing Kit DMX
Dimensions (Height x Width x Depth)	30 x 88 x 122 mm	Full product code	871951494526599
Ingress protection code	IP20 [Finger-protected]	Order code	94526599
Accessory color	Black	Material Nr. (12NC)	911401746102

Uni DMX controls and accessories

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514945265
Numerator - Packs per outer box	12

EAN/UPC - Case	8719514945265
----------------	---------------

Dimensional drawing

