

ZXP399 Addressing Kit
DMX

911401746102



Uni DMX controls and accessories, 6 to 24 DC V, IP20 |
Finger-protected, Yes, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

Operating and Electrical

Input Voltage	6 to 24 DC V
Line Frequency	- Hz

Mechanical and Housing

Overall length	122.4 mm
Overall width	88.15 mm
Overall height	30 mm
Dimensions (Height x Width x Depth)	30 x 88 x 122 mm
Ingress protection code	IP20 [Finger-protected]
Accessory color	Black
Net Weight (Piece)	0.260 kg

Approval and Application

CE mark	Yes
---------	-----

Product Data

Order product name	ZXP399 Addressing Kit DMX
Full product name	ZXP399 Addressing Kit DMX
Full product code	871951494526599
Order code	94526599
Material Nr. (12NC)	911401746102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514945265
Numerator - Packs per outer box	12
EAN/UPC - Case	8719514945265

Dimensional drawing

