



ZXP399 DMX Controls and Accessories

ZXP399 Addressing Kit DMX

ZXP399 DMX Controls and Accessories, 6 to 24 DC V, IP20 | Finger-protected, Yes, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include a main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6,000 DMX universes. Stand-alone Controller: Fits all medium applications with up to 700 DMX universes. Wiring accessories include leader and jump cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low-power repeater that can amplify the DMX signal for up 100 metres.

Product data

Operating and Electrical		Dimensions (height x width x depth)	
Input Voltage	6 to 24 DC V	30 x 88 x 122 mm	
Line Frequency	- Hz	Ingress protection code	
		IP20 [Finger-protected]	
		Accessory colour	
		Black	
		Net Weight (Piece)	
		0.260 kg	
Mechanical and Housing		Approval and Application	
Overall length	122.4 mm		
Overall width	88.15 mm	CE mark	
Overall height	30 mm	Yes	

ZXP399 DMX Controls and Accessories

Product Data	
Order product name	ZXP399 Addressing Kit DMX
Full product name	ZXP399 Addressing Kit DMX
Full EOC	871951494526599
Order code	911401746102
Material no. (12 NC)	911401746102

Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514945265
Numerator – packs per outer box	12
EAN/UPC – Case	8719514945265

Dimensional drawing

