



# UniFlood M G2

## BVP353 30LED RGB 220V L30 10 DMX

UniFlood M G2, 2495 lm, 60 W, RGB, Dynamic DMX/RDM, Safety class I

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Warnings and Safety

- For outdoor use only.

### Product data

| General Information                |             | Effective projected area |  |
|------------------------------------|-------------|--------------------------|--|
| Driver included                    | Yes         | 0.047 m <sup>2</sup>     |  |
| Lighting Technology                | LED         | Operating and Electrical |  |
| Value ladder                       | Performance | Input Voltage            | 220 to 240 V   |
| Light Technical                    |             | Line Frequency           | 50 to 60 Hz  |
| Luminous Flux                      | 2,495 lm    | Power Consumption        | 60 W   |
| Correlated Color Temperature (Nom) | -           | Power Factor (Fraction)  | 0.9  |
| Luminous Efficacy (rated) (Nom)    | 42 lm/W     | Connection               | Flying leads/wires and 2 Push-in connector 4-pole                        |
| Color rendering index (CRI)        | >80         | Cable                    | Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole |
| Light source color                 | RGB         |                          |  |

## UniFlood M G2

|                                     |  |
|-------------------------------------|--|
| Protection class IEC                | Safety class I                               |
| <b>Controls and Dimming</b>         |  |
| Dimmable                            | Yes  |
| Control interface                   | Dynamic DMX/RDM                              |
| <b>Mechanical and Housing</b>       |  |
| Housing Material                    | Aluminum extruded                            |
| Optical cover material              | Acrylate                                     |
| Housing Color                       | Dark gray                                    |
| Overall length                      | 293 mm                                       |
| Overall width                       | 140 mm                                       |
| Overall height                      | 149 mm                                       |
| Dimensions (Height x Width x Depth) | 149 x 140 x 293 mm                           |
| Ingress protection code             | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code        | IK06 [1 J]                                   |
| Optical cover type                  | Clear glass                                  |
| Net Weight (Piece)                  | 3.650 kg                                     |
| <b>Approval and Application</b>     |  |
| Flammability mark                   | For mounting on normally flammable surfaces  |

|  |                                  |
|--|----------------------------------|
| CE mark                                    | Yes                              |
| Ambient temperature range                  | -40 to +50 °C                    |
| <b>Initial Performance (IEC Compliant)</b> |                                  |
| Luminous flux tolerance                    | +/-10%                           |
| Power consumption tolerance                | +/-10%                           |
| <b>Product Data</b>                        |                                  |
| Order product name                         | BVP353 30LED RGB 220V L30 10 DMX |
| Full product name                          | BVP353 30LED RGB 220V L30 10 DMX |
| Full product code                          | 871951492613499                  |
| Order code                                 | 92613499                         |
| Material Nr. (12NC)                        | 911401746923                     |
| Numerator - Quantity Per Pack              | 1                                |
| EAN/UPC - Product/Case                     | 8719514926134                    |
| Numerator - Packs per outer box            | 4                                |
| EAN/UPC - Case                             | 8719514926134                    |

## Dimensional drawing

