

# UniFlood M G2

## BVP353 72LED 30K 220V L57 45 DMX

UniFlood M G2, 11875 lm, 150 W, 830 warm white, Dynamic DMX/RDM, Safety class I

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Warnings and Safety

- For outdoor use only.

### Product data

| General Information | |
|---|---|
| **Driver included** | Yes |
| **Lighting Technology** | LED |
| **Value ladder** | Performance |

| Light Technical | |
|---|---|
| **Luminous Flux** | 11,875 lm |
| **Correlated Color Temperature (Nom)** | 3000 K |
| **Luminous Efficacy (rated) (Nom)** | 79 lm/W |
| **Color rendering index (CRI)** | >80 |
| **Light source color** | 830 warm white |

| | |
|---|---|
| **Effective projected area** | 0.078 m² |

| Operating and Electrical | |
|---|---|
| **Input Voltage** | 220 to 240 V |
| **Line Frequency** | 50 to 60 Hz |
| **Inrush current** | 60 A |
| **Power Consumption** | 150 W |
| **Power Factor (Fraction)** | 0.95 |
| **Connection** | Flying leads/wires and 2 Push-in connector 4-pole |
| **Cable** | Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole |

# UniFlood M G2

| | |
|---|---|
| **Protection class IEC** | Safety class I |

## Controls and Dimming

| | |
|---|---|
| **Dimmable** | Yes |
| **Control interface** | Dynamic DMX/RDM |

## Mechanical and Housing

| | |
|---|---|
| **Housing Material** | Aluminum extruded |
| **Optical cover material** | Acrylate |
| **Housing Color** | Dark gray |
| **Overall length** | 569 mm |
| **Overall width** | 140 mm |
| **Overall height** | 149 mm |
| **Dimensions (Height x Width x Depth)** | 149 x 140 x 569 mm |
| **Ingress protection code** | IP66 [Dust penetration-protected, jet-proof] |
| **Mech. impact protection code** | IK06 [1 J] |
| **Optical cover type** | Clear glass |
| **Net Weight (Piece)** | 6.800 kg |

## Approval and Application

| | |
|---|---|
| **Flammability mark** | For mounting on normally flammable surfaces |
| **CE mark** | Yes |
| **Ambient temperature range** | -40 to +50 °C |

## Initial Performance (IEC Compliant)

| | |
|---|---|
| **Luminous flux tolerance** | +/-10% |
| **Initial chromaticity** | 4 SDCM |
| **Power consumption tolerance** | +/-10% |

## Product Data

| | |
|---|---|
| **Order product name** | BVP353 72LED 30K 220V L57 45 DMX |
| **Full product name** | BVP353 72LED 30K 220V L57 45 DMX |
| **Full product code** | 871951492782799 |
| **Order code** | 92782799 |
| **Material Nr. (12NC)** | 911401748613 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8719514927827 |
| **Numerator - Packs per outer box** | 4 |
| **EAN/UPC - Case** | 8719514927827 |

## Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.